
Side Ported

Bottom Ported

SY3000/5000/7000 Series

Note) 2-position double of rubber seal and manual override with locking function (D, E, F type) are excluded, because they don't comply with safety standard.

How to Order Valves (With mounting screw)



1 Series

3	SY3000
5	SY5000
7	SY7000

2 Type of actuation

1	1 2 *1 2-position	Single
2 *1		Double
3	3 4 3-position	Closed center
4		Exhaust center
5		Pressure center
A *2	A*2 B*2 C*2 4-position dual 3-port	N.C./N.C.
B *2		N.O./N.O.
C *2		N.C./N.O.

*1 Only the metal seal type is available for the 2-position double valve.

*2 Only the rubber seal type is available for the 4-position dual 3-port valve.

Seal type

-	
0	Rubber seal
1	Metal seal

4	Pilot	type

Nil	Internal pilot External pilot	
R		

5 Back pressure check valve (Built-in valve type)

Nil	None
Н	Built-in

* Only the rubber seal type is available.

 The back pressure check valve is not available for the 3-position type or the SY7000.

6 Pilot valve opti

Pilot valve option			
	Nil	Standard (0.7 MPa)	
	В	Quick response type (0.7 MPa)	
	K *1	High pressure type (1.0 MPa)	

*1 Only the metal seal type is available for the high pressure type.

Coil type

Nil Standard	
т	With power saving circuit (Continuous duty type)
* Be sure to select the power saving circuit	

type if the valve is to be continuously energized for long periods of time.

8 Rated voltage

5	24 VDC	
6	12 VDC	

Uight/surge voltage suppressor and common specification

Symbol	With light	Surge voltage suppressor	Common specification
Nil	—	—	
R	—		Non-polar
U	•	•	
S			Positive
Z	•		common
NS			Negative
NZ	\bullet		common

 Only "Z" and "NZ" types are available with a power saving circuit.

Manual override



Type of mounting screw

Nil	Round head combination screw	
В	Hexagon socket head cap screw	
К	Round head combination screw (Drop prevention type)	
Н	Hexagon socket head cap screw (Drop prevention type)	




Plug-in

Top Ported

SY3000/5000/7000 Series

Note) 2-position double of rubber seal and manual override with locking function (D, E, F type) are excluded, because they don't comply with safety standard.

How to Order Valves (With mounting screw)



1 Series

U Sei	165
3	SY3000
5	SY5000
7	SY7000

2 Type of actuation

<u> </u>		
1	0 maaitian	Single
2 *1	2-position	Double
3		Closed center
4	3-position	Exhaust center
5		Pressure center
A *2	4-position	N.C./N.C.
B *2	dual	N.O./N.O.
C *2	3-port	N.C./N.O.

*1 Only the metal seal type is available for the 2-position double valve.

*2 Only the rubber seal type is available for the 4-position dual 3-port valve.

3 Seal type

0	Rubber seal
1	Metal seal

4 Pilot type

Nil	Internal pilot
R	External pilot

5 Back pressure check valve (Built-in valve type)

Nil	None	
Н	Built-in	

 Only the rubber seal type is available.
The back pressure check valve is not available for the 3-position type or the SY7000.

6 Pilot valve option

Nil	Standard (0.7 MPa)
В	Quick response type (0.7 MPa)
K *1	High pressure type (1.0 MPa)

*1 Only the metal seal type is available for the high pressure type.

Coil type

N 111		
Nil	Standard	
т	With power saving circuit	
	(Continuous duty type)	

* Be sure to select the power saving circuit type if the valve is to be continuously energized for long periods of time.

8 Rated voltage

5	24 VDC
6	12 VDC
•	12.120

9 Light/surge voltage suppressor and common specification

Symbol	With light	Surge voltage suppressor	Common specification
Nil	—	—	
R	—		Non-polar
U	•		
S	—		Positive
Z		•	common
NS	—		Negative
NZ			common

 Only "Z" and "NZ" types are available with a power saving circuit.

Manual override



A, B port size

rineau pipilig		
Symbol	Port size	Applicable series
M5	M5 x 0.8	SY3000
01	1/8	SY5000
02	1/4	SY7000

One-touch fitting (Metric)

••	• ···• ·•• ·•• ·······················			
Symbol	A, B port	SY3000	SY5000	SY7000
C2	ø2		—	_
C3	ø3.2		—	—
C4 C6	ø4			—
C6	ø6			
C8	ø8	—	•	
C10	ø10	—	—	
C12	ø12	_	_	

One-touch fitting (Inch)

Symbol	A, B port	SY3000	SY5000	SY7000
N1	ø1/8"		—	—
N3	ø5/32"			—
N7	ø1/4"			
N9	ø5/16"	—		
N11	ø3/8"	—	—	

Thread type

Nil	Rc
F	G
Ν	NPT
Т	NPTF

Only Nil is available for M5.

B Type of mounting screw

Nil	Round head combination screw
В	Hexagon socket head cap screw
к	Round head combination screw (Drop prevention type)
н	Hexagon socket head cap screw (Drop prevention type)

