

3 Port Solenoid Valve Direct Operated Poppet Type **VT307 Series** Rubber Seal

How to Order

V T 307 - **5 G** **1** - **01** - **F** -

Body type

T	Body ported
O	For manifold

Valve option

Nil	Standard type
E	Continuous duty type
Y	Energy-saving type
V	Vacuum specification type
W	Energy-saving type, Vacuum specification type

Pressure specifications

Nil	Standard type (0.7 MPa)
K	High-pressure type (1 MPa)

Rated voltage

1	100 VAC, 50/60 Hz
2	200 VAC, 50/60 Hz
3	110 VAC, 50/60 Hz
4	220 VAC, 50/60 Hz
5	24 VDC
6	12 VDC
7	240 VAC, 50/60 Hz

Electrical entry

Grommet		DIN terminal	
G : 300 mm lead wire		D : With connector	
H : 600 mm lead wire		DO : Without connector	

CE-compliant

Nil	None
Q	CE-compliant*

* Electrical entry and light/surge voltage suppressor: D/DO/DZ/DOZ only

Bracket

Nil	None
F	With bracket

Thread type

Nil	Rc
F	G
N	NPT
T	NPTF

Port size

Nil	Without port (For manifold)
01	1/8 (6A)
02	1/4 (8A)

Light/Surge voltage suppressor

Nil	None
S	With surge voltage suppressor (Grommet type only)
Z	With light/surge voltage suppressor (DIN terminal type only)

SMC validation products have been validated based on ISO 13849-2: 2012 Annex A, B & D.