
Rubber Seal 3 Port/Pilot Poppet Type Body Ported/Single Unit

VP300/500/700 Series

How to Order

Note) Manual override with locking function (D and E type) are excluded, because they don't comply with safety standard.



* LN and MN types are with 2 sockets.

Note) With the same specifications as the DC type, all lead wire entries for the 24 VAC type are CE marking compliant.

⚠ Caution

When using the surge voltage suppressor type, residual voltage will remain.

SMC validation products have been validated based on ISO 13849-2: 2012 Annex A, B & D.




Rubber Seal 3 Port/Pilot Poppet Type **Base Mounted/Single Unit**

VP300/500/700 Series

How to Order

Note) Manual override with locking function (D and E type) are excluded, because they don't comply with safety standard.



* LN and MN types are with 2 sockets

€

DC

CF-AC No

Note) With the same specifications as the DC type, all lead wire entries for the 24 VAC type are CE marking compliant.

CE

SMC validation products have been validated based on ISO 13849-2: 2012 Annex A, B & D.

