

2/3 Port Mechanical Valve

VM200 Series



How to Order

VM2 **3** 0 **02** - **00** **A** - **B**

• **Number of ports**

2	2 port
3	3 port
5	5 port (Twist selector 3 position only)

• **Body option**

Nil	Side mounting
U	With bottom mounting thread

• **Port size**

02	R1/4
N02	NPT1/4
F02	G1/4

• **Bracket option**

Nil	None
B	With bracket

Note) Applicable only to side mounting type.
However, not applicable to twist selector
(3 position) and foot pedal.
Bracket is shipped together, but not
assembled.

• **Suffix for actuator***

S	Hard steel roller	
R	Red	Color of push button, selector
B	Black	
G	Green	
Y	Yellow	

* Refer to the table shown [here](#)
for combinations of actuator
type and suffix.

• **Actuator type***

00	Basic
30	Push button (Mushroom)
32	Push button (Extended)
33	Push button (Flush)

SMC validation products have been validated
based on ISO 13849-2: 2012 Annex A & B.