
Air Operated Insert Bushing Integrated Fitting Type

LVC Series



How to Order Valve (Single Type)



03	3 x 2						
04	4 x 3						
06	6 x 4	0					
08	8 x 6						
10	10 x 8		0	•			
12	12 x 10			0			
19	19 x 16				0	•	
25	25 x 22					0	
Inch s	Inch size						
03	1/8" x 0.086"						

Metric size

03	1/8" x 0.086"					
05	3/16" x 1/8"					
07	1/4" x 5/32"	0				
11	3/8" x 1/4"		0	•		
13	1/2" x 3/8"			0	•	
19	3/4" x 5/8"				0	
25	1" x 7/8"					0

○Basic size ●With reducer

*1: Applicable fitting for body class 6 is LQ1. *2: Refer to the Web Catalog for details of the applicable tubing sizes.

		Model	LVC20	LVC30	LVC40	LVC50	LVC60
	Tubing O.D.	diameter	ø4	ø8	ø10	ø16	ø22
		Metric	3, 4, 6	6, 8, 10	10, 12	12, 19	19, 25
Туре	Symbol	Inch ve type	1/8, 3/16, 1/4	1/4, 3/8	3/8, 1/2	1/2, 3/4	3/4, 1
Basic	ÿPA ÿPE B A B H		0	0	0	0	0
		N.O.	0	0	0	0	0
With flow rate adjustment	ÿPA B I I A	N.C.	0	0	0	0	0
With bypass	ÿPA B A N.C.	N.C.	_	0	0	0	_
With flow rate adjustment & bypass	ÿPA B A N.C.	N.C.	_	0	0	0	_
With indicator	⊌ PA B I I A S N.C.	N.C.	0	0	0	0	0

SMC validation products have been validated based on ISO 13849-2: 2012 Annex A & B.

