Regulator AR20-B to AR60-B Regulator with Backflow Function AR20K-B to AR60K-B

How to Order

How to Order											
٩F	83	0 K - [F 0 6 (Option/S specifica	Semi-st ation is	andard s	ymbol: W , indicate	e each fo /hen more in alphan	than on	
			Question	Description		0					
			Symbol	Description		Body size					
						20	25	30	40	50	60
2	With backflow		Nil	Without backflow function		•	•	•		•	
		function	K *1	With backflow function		•					
			+ Nil	Rc		•		•		•	
3	Thread type		N	NPT	$\dashv \vdash$	•			•		
			F	G		-	•	•	•	Ŏ	Ĭ
			+			-	-	-		-	
			01	1/8			_	—	—	—	—
4			02	1/4						_	—
		Port size	03	3/8		—	•			—	-
		1 011 0120	04	1/2		—	_			_	
			06	3/4		—	_			•	-
			10	1		—	—	—	—	•	
			+	APAL		•					
		Mounting	Nil	Without mounting option		•	•	•	•	•	
	a		B *3	With bracket With set nut (for panel mount)		•	•			•	-
Option *2	:		│ <u>H</u> +	with set hut (for panel mount)		•	•	•		_	
			Nil	Without pressure gauge						•	
	-	Pressure gauge ^{*4}	E	Square embedded type pressure gauge (with limit indicate	or)	•		•	•		
	b		G	Round type pressure gauge (with limit indicator)		Ŏ	•	•	•	ĕ	Ŏ
			M	Round type pressure gauge (with color zone)		•	•	•	•	ě	Ĭ
			+				-				
	c	Set pressure *5	Nil	0.05 to 0.85 MPa setting		•				•	
			1	0.02 to 0.2 MPa setting		•					
			+								
	d	Exhaust mechanism	Nil	Relieving type		•	•			•	
pr			N	Non-relieving type		\bullet				•	
Semi-standard			+	There allow allows the first states		•					
	е	Flow direction	Nil	Flow direction: Left to right		•	•	•	•	•	
			│ R +	Flow direction: Right to left		•	•		U	•	
Sei			 ∣ Nil	Downward							
	f	Knob	Y	Upward		-					
			+	opinara		-	•	-	-	•	
		D	Nil	Name plate and pressure gauge in imperial units: MPa	. [•				•	
	g	g Pressure unit	Z *6	Name plate and pressure gauge in imperial units: psi		O*7	0*7	0*7	0*7	0*7	0*
			+			I					
	6	ecial order	Nil	Rubber material: Nitrile rubber specification				•		•	
	Sh		X155	Rubber material: Fluorine rubber specification		•	-				

*1 Set the inlet pressure to at least 0.05 MPa higher than the set pressure.

*2 Options B, G, H, M are not assembled and supplied loose at the time of shipment.
 *3 Assembly of a bracket and set nuts (applicable to the AR20(K)-B to AR40(K)-B).

Including 2 mounting screws for the AR50(K)-B and AR60(K)-B *4 When the pressure gauge is attached, a 1.0 MPa pressure gauge will be fitted for

*4 When the pressure gauge is attached, a 1.0 MPa pressure gauge will be fitted for standard (0.85 MPa) type. 0.4 MPa pressure gauge for 0.2 MPa type.
*5 Pressure can be set higher than the specification pressure in some cases, but use

*5 Pressure can be set higher than the specification pressure in some cases, but use pressure within the specification range. *6 For pipe thread type: NPT.

This product is for overseas use only according to the new Measurement Act. (The SI unit type is provided for use in Japan.)

Cannot be used with M: Round type pressure gauge (with color zone). Available by request for special.

The digital pressure switch will be equipped with the unit selection function, setting to psi initially.

*7 O: For pipe thread type: NPT only

SMC validation products have been validated based on ISO 13849-2: 2012 Annex A & B.

