Simple Specials: -XC15: Change of Tie-rod Length


The following changes are dealt with through the Simple Specials System. Please contact your local sales representative for more details.

9 Change of Tie-rod Length

Cylinder with M dimension for tie-rod length changed from the standard length.

Series	Description	Model	Action	Note			
CA2	Standard type	CA2-Z	Double acting, Single rod				
	Standard type	CA2W-Z	Double acting, Double rod				
	New wetering and these	CA2K	Double acting, Single rod	Applicable to ø40 to ø63			
	Non-rotating rod type	CA2KW	Double acting, Double rod	Applicable to ø40 to ø63			
	Air-hydro cylinder	CA2H	Double acting, Single rod				
	End lock cylinder	CBA2	Double acting, Single rod				
	Smooth cylinder	CA2Y-Z	Double acting, Single rod				
	Others devide ware	CS1	Double acting, Single rod				
CS1	Standard type	CS1W	Double acting, Double rod				
	Low friction type	CS1□Q	Double acting, Single rod	Applicable to ø125 to ø160			
	Standard type	CS2	Double acting, Single rod				
	Standard type	CS2W	Double acting, Double rod				
CS2	Long stroke	CS2-V	Double acting, Single rod	Applicable to ø180 to ø320			
	Axial centralized piping	CS2□P	Double acting, Single rod	Applicable to ø180 to ø250			
	Smooth cylinder	CS2Y	Double acting, Single rod	Applicable to ø125 to ø160			
01140	Outlined an with leads	CNA2	Double acting, Single rod				
CNA2	Cylinder with lock	CNA2W	Double acting, Double rod				
		CV3	Double acting, Single rod				
<i></i>	Valve mounted cylinder	СУЗК	Double acting, Single rod	Applicable to ø40 to ø63			
CV	valve mounted cylinder	CVS1	Double acting, Single rod				
		CVS1K	Double acting, Single rod	Applicable to ø40 to ø63			

CA2, CNA2, CV series



▲ Precautions

1. To order, specify the M dimension as well as the part number. 2. SMC will make appropriate arrangements if no dimension, tolerance, or finish instructions are given in the diagram.

3. Tie-rod length changeable range is described in the below.

The M dimension of the bracket mounting side of Flange (F, G), Clevis (C, D) types cannot be specified.

Tie-rod Length Changeable Range

		-						()
Model	CA2, CNA2, CV				CS1			
Bore size (mm)	All bore size	125	140	160	180	200	250	300
M Min.	0	15	5.5	18	20.5	22	26	32.5
M Max.	300 (1)				110			


Note 1) The maximum value of M on the rod side for the CNA2 series is 50

Tie-rod Length Changeable Bange

Tie-rod Length Changeable Range (mm)														
Model	CS2													
Bore size (mm)	125			140	160 180		200		250		320			
Mounting bracket	L	B, F, G, C, D, T	L	B, F, G, C, D, T	L	B, F, G, C, D, T	L	B, F, G, C, D, T	L	B, F, G, C, D, T	L	B, F, G, C, D, T	L	B, F, G, C, D, T
M Min.	20	12	21	12	23	14	27	17	28	18	33	21	38	0
M Max.	110													

CS1, CS2 series

(mm)



Symbol

-XC15