**Environmentally Resistant** 

RoHS

3-Finger Air Gripper


Ø32, Ø63

Applicable for environments with water droplets and dust




# Durability 1 0 times or more

- \*1 Compared with the standard model in environments with water splashing
- A variety of scrapers and Lube-retainers for various applications (environments) are available.




■ Improved attachment position reproducibility



\* The attachment, positioning pin, and bolts should be ordered separately by the customer. Solid state auto switches are mountable.





 Refer to pages 4 and 5 for details on the depth.




Solid state auto switch




# MHS3-X6708□ Model Selection

#### **Model Selection Example**



#### **Model Selection Illustration**



When gripping a workpiece as in the figure to the left, and with the following definitions,

- 3: Number of fingers
- F: Gripping force [N]
- μ: Coefficient of friction between the attachments and the workpiece
- m: Workpiece mass [kg]
- g: Gravitational acceleration (9.8 m/s²)
- mg: Workpiece weight [N]

the conditions under which the workpiece will not drop are

 $3 \times \mu F > mg$ 

and therefore,

$$F > \frac{mg}{3 \times \mu}$$

With "a" as the safety margin, **F** is determined as follows:

$$F = \frac{a \times mg}{3 \times \mu}$$

# Multiples of Gripping Force by Workpiece Mass

#### Number of fingers: When n = 3

• SMC performs calculations allowing for impacts which occur during normal transfer, etc., using a safety margin of a = 4.


When $\mu$ = 0.2	When μ = 0.1
$F = \frac{mg}{3 \times 0.2} \times 4$ $= 10 \times mg$	$F = \frac{mg}{3 \times 0.1} \times 4$ $= 20 \times mg$
<b>†</b>	<b>^</b>
10 x Workpiece weight	20 x Workpiece weight

- $\ast$  · Even in cases where the coefficient of friction is greater than  $\mu=0.2,$  for reasons of safety, select a gripping force which is at least 7 to 13 times greater than the workpiece weight, as recommended by SMC.
  - If high acceleration, or impact forces are encountered during motion, a further margin should be considered.



#### **Gripping Point**

- The workpiece gripping point distance should be within the gripping force ranges given for each pressure in the effective gripping force graphs below.
- If operated with the workpiece gripping point beyond the indicated ranges, an excessive offset load will be applied to the sliding section of the fingers, which can have an adverse effect on the service life of the product.




L: Gripping point distance

#### **Effective Gripping Force**

• Indication of effective gripping force The effective gripping force shown in the graphs to the right is expressed as F, which is the thrust of one finger when all 3 of the fingers and attachments are in full contact with the workpiece as shown in the figure





**External grip** 




Internal grip


#### **External Gripping Force**





#### **Internal Gripping Force**






# **Environmentally Resistant 3-Finger Air Gripper**

# MHS3-X6708

ø32, ø63

#### **How to Order**




Applicable Auto Switches / Refer to the Web Catalog for further information on auto switches.

Туре	Special function	Electrical	Indicator	Wiring Load voltage		ıge	Auto swit	Lead wire length [m]*2				Pre-wired	Applicable load						
Type	Special function	entry	light	(Output)	DC AC		Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector	or Applicable load					
_	_				3-wire (NPN)		5 V,		VA6W	M9N	•	•	•	0	0	IC aireuit			
switch			3-wire (PNP)	1	12 V		M9PV	M9P	•	•	•	0	0	IC circuit					
S		Grommet Yes	2-wire	12 V		M9BV	M9B	•	•	•	0	0	_						
욘	Di			3-wire (NPN)	<b>⊣</b>	5 V,	M9NWV	M9NW	•	•	•	0	0	10	Б				
an	Diagnostic indication (2-color indicator)		Yes	3-wire (PNP)		24 V 12 V	24 V   12	24 V	_	M9PWV	M9PW	•	•	•	0	0	IC circuit	Relay, PLC	
tate	Water resistant			2-wire	2-wire	12 V		M9BWV	M9BW	•	•	•	0	0	_	FLC			
S						3-wire (NPN)	5 V.	1	,T [		M9NAV*1	M9NA*1	0	0	•	0	0	IC aireuit	
(2-color indicate		2-color indicator)		3-wire (PNP)	PNP)	12 V		M9PAV*1	M9PA*1	0	0	•	0	0	IC circuit				
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_				

- \*1 Water-resistant type auto switches can be mounted on the above models, but SMC cannot guarantee water resistance.
- 0.5 m..... Nil (Example) M9NW (Example) M9NWL \*2 Lead wire length symbols: 3 m..... L (Example) M9NWM (Example) M9NWZ
- Solid state auto switches marked with "O" are produced upon receipt of order.
- \* When using the 2-color indicator type, please set it so that the indicator lights up red to ensure air gripper detection at the proper position.

#### Specifications

Model		MHS3-32D-X6708□	MHS3-63D-X6708□			
Bore size		ø32	ø63			
Fluid		Air				
Action		Double acting				
Operating pressur	e	0.2 to 0.6 MPa				
Ambient and fluid te	mperatures	−10 to 60°C				
Repeatability		±0.01 mm				
Gripping force (0.5 MPa, L = 30 mm)	External gripping force	74 N	335 N			
	Internal gripping force	82 N	359 N			
Finger stroke*1		4 mm	8 mm			
Seal material		NBR				
Max. operating frequency		60 c.p.m.				
Lubricant		Non-lube				
Weight		600 g	2,400 g			



Double acting: Internal grip





#### Replacement Parts

#### Cover assembly part number


**MHS3 - A** – X6708 Bore size Specifications A With heavy-duty scraper + Lube-retainer 32 32 mm 63 With water-resistant scraper + Lube-retainer With double Lube-retainer


No.	Description	X6708 A	X6708 B	X6708 C
1	Finger cover	•	•	•
2	Heavy-duty scraper	•	_	_
3	Water-resistant scraper		•	
4	Lube-retainer	•	•	•
5	O-ring	•	•	•
6	Hexagon socket head cap screw*1	•	•	•



- \*1 Hexagon socket head cap screws for mounting (4 pcs.) are shipped together with the product
- X6708A (With heavy-duty scraper + Lube-retainer)

X6708B (With water-resistant scraper + Lube-retainer)








# Environmentally Resistant 3-Finger Air Gripper MHS3-X6708

#### **Dimensions**

# OR OR

#### MHS3-32D-X6708□

(The dimensions of the model with a heavy-duty scraper + Lube-retainer, the model with a water-resistant scraper + Lube-retainer, and the model with a double Lube-retainer are the same.)



- \*1 Connect piping to the breathing port so that the dust, water, etc., in the surrounding atmosphere does not get into the product, and open the port to a safe place.
- \*2 Only applies to the model with a heavy-duty scraper or water-resistant scraper

Auto switch mounting groove dimensions (2 locations, same shape)




### *MHS3-X6708*□

#### **Dimensions**

#### MHS3-63D-X6708□

(The dimensions of the model with a heavy-duty scraper + Lube-retainer, the model with a water-resistant scraper + Lube-retainer, and the model with a double Lube-retainer are the same.)




- \*1 Connect piping to the breathing port so that the dust, water, etc., in the surrounding atmosphere does not get into the product, and open the port to a safe place.
- \*2 Only applies to the model with a heavy-duty scraper or water-resistant scraper

(2 locations, same shape)

# MHS3-X6708□ Related Products


# Wide Type Parallel Style Air Gripper/MHL2-X85/-X86 Ø10, Ø16, Ø20, Ø25, Ø32, Ø40

- In micro-powder (10 to 100 μm) environments With double Lube-retainer (-X85)
  - \* Prevents particles and foreign matter from entering the gripper The Lube-retainer ensures a consistent film of grease, improving gripper durability.




## In dusty environments With heavy-duty scraper + Lube-retainer (-X86□)

- Applicable for environments containing particles or foreign matter A grease film is formed on the rod by the Lube-retainer in order to improve durability.
- \* Seal material can be NBR or fluororubber.



# Coolant-resistant Air Gripper/MHZJ2-32D-X6544 Ø32



- $\bullet$  Increased resistance to splashing coolant
- Finger portion with collar protected by dust cover prevents contamination.
- $\bullet$  Dust cover and plate connection prevent contamination.



