
Flat

**Flat Pad** 

Pad diameter Ø10, Ø15, Ø20, Ø25, Ø30

MT: Thin flat type (With groove)

Symbol/Form



**How to Order** 

**ZP2-B10 MT N** Pad unit

Pad diameter

**B15** 

**B20** 

**B25** 

B30

Symbol Pad diameter

B10 Ø10


ø15

ø20

ø25

ø30

# Pad material



	Pad form
Symbol	Form
MT	Thin flat type (With groove)

- Not suitable for transferring workpieces which apply a load.
  Wrinkling may be generated depending on the sheet thickness. Confirm the thickness before use.
- ■Supports blast type\*1 pads

■For the adsorption of thin sheets or film

Reduced deformation of flat surfaces during adsorption

\*1 Allows for the easy removal of workpieces

<b></b>		•	Conductive Heart	
GS		S	Conductive silicone rubber	
	*1	Со	mpliant with the FDA (USA Food	and Dru
		Ad	ministration) regulation 21CFR§	177.260
		for	"Rubber articles intended for repe	eated us
		A	allegation and also resolved a few (ID), because of	lancal cultural land

\*2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Addi-


tives, etc." (Ministry of Health and Welfare Notification No. 370, 1959).


ZP2-B25MT□


**Mounting Bracket Part Nos.** 


Adapter Assembly


# **Dimensions: Pad Unit**















ø18

ø6



2








# ZP2-B30MT□ ø10

# **Adapter Mounting Dimensions**

If an adapter will be made by the customer, design the adapter with the dimensions shown below.








The R part has to be smooth with no corners.







Gasket\*3 Symbol Gasket Without gasket With gasket

Connection thread: Only for option "H5" can either "Without gasket" or "With gasket" be selected. When "Nil" is selected for option "A5," it comes with a gasket.

# Connection thread

Symbol	Thread size	Adapter type	
	M5 x 0.8 (Male thread)		
H5	M5 x 0.8 (Male thread)	Hexagon socket head	
B5	M5 x 0.8 (Female thread)	Hexagon O.D.	

\* If used without a gasket, vacuum leakage may occur. Therefore, when ordering the type without a gasket, be sure to use a commerciallyavailable gasket or sealant when mounting.

ø30

B30

Symbol Material NBR Silicone rubber\*1, \*2 S FKM GN Conductive NBR GS Conductive silicone rubber


Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use" Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food

and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959).


**Dimensions: With Adapter** \* Connection thread: The male thread drawings show the type with a gasket.

#### ZP2-TB10MT□-H5G

# Width across flats 2.5 ø8 M5 x 0 8 (0.3)ø1.5 ø10 ø11




ø16




# ZP2-TB25MT□-H5G


(With groove)




### ZP2-TB30MT□-H5G




## ZP2-TB10MT□-B5




ZP2-TB15MT□-B5




### ZP2-TB20MT□-B5



ZP2-TB25MT□-B5





ZP2-TB30MT□-B5








**Dimensions: With Adapter** 














# Adapter Assembly

Flat Pad ZP2 Series



**Mounting Bracket Assembly** 

		Cumhal	<b>●</b> Pad diameter symbol						
			Symbol	B10	B15	B20	B25	B30	
70	nection	thread	M5 x 0.8	<b>A</b> 5	ZP2A-M08P		ZP2A-M09P		
A Adapter		Male		H5G	ZP2A-M02P		ZP2A-M03P		
(4)		Female thread	M5 x 0.8	B5	ZP2A	-M04		ZP2A-M07	

<b>B</b> Gasket	10 pcs.*1	ZP-5G2
(Single unit)	100 pcs.*1	M-5G2

<sup>\*1</sup> The gasket (single unit) sales unit is shown.

#### <Flat Pad Precautions>

1. When mounting the product, be sure to tighten the product within the recommended tightening torque range.

Model	Connection thread	Tightening torque [N·m]
ZP2-TB(10, 15)MT□-(A5, H5G)	M5 x 0.8 (Male thread)	0.9 to 1.1
ZP2-TB(20, 25, 30)MT□-(A5, H5G)		1.5 to 1.7

2. When mounting the adapter with hexagon socket head specification (Product number suffix "-H5(G)"), be sure to mount the pad only after the adapter has been mounted on the device.

If a hexagon wrench is inserted into the adapter with the pad already mounted, the pad may be damaged.

Combining the adapter with a pad may be difficult depending on the pad diameter and pad material. In such cases, we recommend ordering the "-A5" specification hexagon adapter with a pad, which can be connected to the device as is.