
Pressure Control Valve AP100

Pressure greater than the set pressure is released into the atmosphere, which allows pressure in the pipe to be maintained.




Application Example

Cylinder cushion



Relief Characteristics

AP100-02




Note) The graph above shows the relief flow when the set pressure rises and falls from 0.1 MPa

Standard Specifications

AP100
1/8, 1/4
Air
1.5 MPa
1.0 MPa
0.05 to 0.69 MPa
-5 to 60°C (No freezing)
part no.: B21-1P
0.12

How to Order



Precautions


Do not use this product as a safety valve.

Definition of safety valves (JIS)

SMC

Valves used for ensuring pressure capacity and piping safety.

Dimensions



ARJ AR425

ARX

AMR ARM

ARP IR□-A

IR

IRV

VEX

SRH SRP

SRF

ITV IC

ITVH

ITVX

PVQ

VY1 VBA VBAT

AP100