Booster Lube ALB900 Series

- Centralized control of multi-point lubrication
- Stable oil feeding with a micromist
- Through the use of a booster, a pressure that is higher than that of the main air passage can be supplied. This difference is used as the mist generating pressure differential. Thus, the pressure drop in the main air passage is minimized.
- Micromist can be constantly supplied by merely adjusting the mistgenerating pressure differential.
- Oil can be replenished by merely opening and closing the oil filler plug without stopping the air line.
- The condition of the generation of micromist can be checked from the oil filler port.

Model	ALB900-10	ALB900-20	ALB900-30				
Port (Bypass lubrication adapter)	Rc 1	Rc 2	3 inch flange				
Port size (Body)	IN: R 1/4 OUT: Rc 1/2						
Fluid	Air						
Proof pressure	1.5 MPa						
Operating pressure range	0.4 to 1.0 MPa						
Operating pressure differential range	0.05 to 0.2 MPa						
Bowl capacity between levels (cm³)	5000						
Recommended lubricant	Turbine oil Class 1 (With no additives), ISO VG32						
Ambient and fluid temperature	5 to 50°C						

Standard Specifications

Accessory	(Option)) Part No.

Bowl material


Weight (kg)

Time		Part no.						
Type	Description Model	ALB900-10	ALB900-20	ALB900-30				
	Bypass lubrication adapter	ALBA90-10	ALBA90-20	ALBA90-30				
Standard accessory	Ball valve	Rc 1/4						
	Ball valve	Rc1∕₂						
Option	Float switch Note)	IS440-1 (Without oil ON) IS440-2 (Without oil OFF)						

Contact — 1a, 1b
Level indication — Bottom limit indication

Epoxy resin with glass fiber, Polycarbonate





AL800 AL900 ALF ALT


ALD ALB

LMU

AEP HEP

ALB900 Series


Piping Example



Operation Control Method

As shown in the diagram below, reverse the position of the function plate of the switching valve for operation control, and place it in the NO position or in the unmarked position. When the control signal is input, select the state of the operation or the stopping of the Booster Lube.


NO position Operation at control signal input
Nil position Stop at control signal input
The 100 VAC, 200 VAC, 220 VAC, 24 VDC, or air pilot type
specification can be applied to the control signal.



Air Consumption

This unit uses a booster to generate a mist generating pressure differential. Therefore, the booster consumes and discharges the air. Data(A) indicates the relationship between this air consumption rate, the set pressure differential, and the pressure of the main air passage (inlet pressure).

Data (A) Air Consumption




Setting of Mist Generation Pressure Differential

Procedure

- Obtain the air consumption flow rate in the downstream of the Booster Lube.
- 2. Obtain the necessary mist generation pressure differential from data(B).

Data(B) Flow — Mist Generation Pressure Differential




EX: How to obtain the mist generating pressure differential if the flow rate obtaine in 1. above is 35 m³/min (ANR) and the line pressure (inlet pressure P₁) is 0.7 MPa:


— Extend horizontally from the point at which the flow rate is 35 m³/min to obtain the noist that interests with P₁ = 0.7 MPa.

the point that intersects with $P_1=0.7\,\text{MPa}$. Furthermore, extend vertically downward from that point to the point that intersects with the graduation line of the mist generating pressure differential. The value of that intersecting point, which is 0.15 MPa, is the mist generating pressure differential that is sought.

3. The mist generating pressure differential setting is performed by adjusting the adjustment screw. The pressure differential (the difference between the boost pressure and the line pressure) is increased by turning the adjustment screw clolckwise, and decreased by turning counterclockwise. To check the pressure differential, switch and operate the manual switching valve to read the difference between the boost pressure (HIGH position) and the line pressure (NORMAL position) as shown below (the pressure gauge that is connected to the manual switching valve). After completing the setting, set the manual switching valve to the position of the line pressure indication. Do not set the mist generating pressure differential to exceed 0.2 MPa.



Mist generation pressure differential setting



⚠ Precautions

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions and pages 387 to 391 for Precautions on every series.

Caution on Design

∆Warning

1. Epoxy resin containing glass fiber and polycarbonate is used in some parts of the Booster Lube. The Booster Lube cannot be used in an environment or in a location that is exposed to synthetic oil, thinner, acetone, alcohol, organic solvets such as ethylene chloride, chemicals such as sulfuric acid or nitric acid, cutting oil, kerosene, gasoline, or a threadlock agent, etc., because they will be damaged.

Piping

If installing an air tank, install it upstream of the bypass oil feed adapter. If it is installed downstream, the micromist could be arrested by the air tank, which could lead to insufficient feeding of oil.

Mounting/Adjustment

∧ Caution

- 1. When setting the pressure differential, if there is a fluctuation in the operating flow rate, set the pressure differential at the higher flow rate range. If it is set in the lower flow rate range, the mist density could become thinner, leading to poor lubrication
- To prevent mist from being generated unnecessarily, if there is no air consumption in the main air passage, operate the switching valve for operation control to stop the operation of the booster.

Maintenance

△Warning

SMC

 Before removing the oil filler plug, loosen it two and half turns to completely release the pressure in the bowl. This will prevent the oil filler plug from flying out.

AL800 AL900

ALF ALT

ALB

LMU ALIP


AEP HEP



1059

ALB900 Series

Construction



Component Parts

No.	Description	Material				
1	Top cover	Aluminum casted				
-	Bottom cover	Aluminum casted				


Replacement Parts

Q'ty
۱ ۱
01 '
0 1
1 1
1
1
eces) 1
(ces)
1
. 1
2
1
1
1 1

^{☐ 1: 100} VAC, 2: 200 VAC, 4: 220 VAC, 5: 24 VDC

Booster Lube ALB900 Series

Dimensions




150 42.7 45 40 35 80

165 76.3 65 60 40 80

ALBA90-10

ALBA90-20

2



AL800 AL900 ALF ALT

ALD

ALB


LMU

ALIP AEP HEP

ALB900 Series Related Product

Strainer

At the terminal of an air pressure line in which a Booster Lube is used, install a strainer (filtration rate of 5 µm) upstream from a metal seal solenoid valve, which is susceptible to dust.



Model	P1	Α	В	С	D	E	J	вв	СС	DD
AF30-02 to 03-A-X2230	Rc1/4, 3/8	53	115.1	14	26.7	30	26.7	35	44	M4 x 0.7 x 0.5
AF40-02 to 04-A-X2230	Rc1/4, 3/8, 1/2	70	147.1	18	35.5	38.4	35.5	47	60	M5 x 0.8 x 8
AF40-06-A-X2230	Rc3/4	75	149.1	20	35.5	38.4	35.5	47	60	M5 x 0.8 x 8
AF50-06 to 10-A-X2230	Rc3/4, 1	90	220.1	24	45	_	45	59	73	M6 x 1
AF60-10-A-X2230	Rc1	95	234.1	24	47.5	_	47.5	63	78	M6 x 1